




LED G25

5.5G25/PER/927-922/FR/G/E26/WGX1FB T20

Philips G25 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	927-922 [CCT of 2700K-2200K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	500 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2700 2200 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	5.5 W
Lamp Current (Nom)	60 mA


Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.75
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	140 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Bulb Shape	G25 (G25)
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star
EyeComfort	Yes
Product Data	
Order product name	5.5G25/PER/927-922/FR/G/E26/WGX1FB T20

LED G25

Full product name	5.5G25/PER/927-922/FR/G/E26/WGX1FB T20
Order code	549535
Material Nr. (12NC)	929001970004
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677549534


Numerator - Packs per outer box	10
EAN/UPC - Case	50046677549539

Dimensional drawing




Product	D	C
5.5G25/PER/927-922/FR/G/E26/WGX1FB T20	3-3/16 inch	4-13/16 inch


Photometric data



Spectral Power Distribution Colour - 5.5G25/PER/927-922/FR/G/E26/WGX1FB T20




Light Distribution Diagram - 5.5G25/PER/927-922/FR/G/E26/WGX1FB T20




General uniform lighting - 5.5G25/PER/927-922/FR/G/E26/WGX1FB T20

LED G25

Lifetime



Life Expectancy Diagram - 5.5G25/PER/927-922/FR/G/E26/WGX1FB T20



Lumen Maintenance Diagram - 5.5G25/PER/927-922/FR/G/E26/WGX1FB T20

