



# MasterClass InstantFit (UL Type-A) T8

### 13T8-6U/MAS/24-835/IF20/P/DIM 10/1

The MasterClass InstantFit T8 lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect. Other lamps claim compatibility but only MasterClass InstantFit (UL Type A) has been proven to work with over 200 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality lamps with no visible flicker and optimized optics. Energy managers will enjoy these lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the MasterClass InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system. With available 70,000 hour life, 7-year limited warranty and a shatter-prevention polycarbonate lens, Philips MasterClass InstantFit TLED lamps deliver benefits for all.

#### **Product data**

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	70,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	835 [CCT of 3500K]

Beam Angle (Nom)	180 degree(s)		
Luminous Flux	2,000 lm		
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3500 K		
Luminous Efficacy (rated) (Nom)	153.00 lm/W		
Color Consistency	<6		
Color rendering index (CRI)	80		
LLMF At End Of Nominal Lifetime (Nom) 70 %			


Datasheet, 2023, October 27 data subject to change

## MasterClass InstantFit (UL Type-A) T8

Operating and Electrical				
Line Frequency	20K to 120K Hz			
Input Frequency	20K to 120K Hz			
Power Consumption	13 W			
Wattage Equivalent	32 W			
Starting Time (Nom)	0.5 s			
Warm-up time to 60% light	0.5 s			
Power Factor (Fraction)	0.9			
Voltage (Nom)	120-277, 347 V			
UL Type	UL Type A			
Temperature				
Ambient temperature range	-4 °F to 113 °F			
T-Case Maximum (Nom)	122 °F			
Controls and Dimming				
Dimmable	Yes			
Mechanical and Housing				
Bulb Finish	Frosted			
Bulb Material	Plastic			
Product Length	23-5/8 inch			
Bulb Shape	T8			

Approval and Application				
Energy Saving Product	Yes			
Approval Marks	RoHS compliance UL certificate DLC			
	compliance			
Energy Consumption kWh/1000 h	- kWh			
Energy Certifications	DLC Standard			
Application Conditions				
can it be used in closed luminaires	Yes			
Product Data				
Order product name	13T8-6U/MAS/24-835/IF20/P/DIM 10/1			
Full product name	13T8-6U/MAS/24-835/IF20/P/DIM 10/1			
Order code	541862			
Material Nr. (12NC)	929001987504			
Numerator - Quantity Per Pack	1			
EAN/UPC - Product/Case	046677541866			
Numerator - Packs per outer box	10			
EAN/UPC - Case	50046677541861			


## Dimensional drawing




Product	D1	D2	A1	A2	A3
13T8-6U/MAS/24-835/	1-1/16 inch	1-1/8 inch	6 inch	22-1/2 inch	1-1/8 inch
IF20/P/DIM 10/1					

## MasterClass InstantFit (UL Type-A) T8


#### Photometric data



Light Distribution Diagram - 13T8-6U/MAS/24-835/IF20/P/DIM 10/1




Spectral Power Distribution Colour - 13T8-6U/MAS/24-835/IF20/P/DIM 10/1




Calculus Photometrics 4.5 Philips Lighting B.V. Pages 1/7

General uniform lighting - 13T8-6U/MAS/24-835/IF20/P/DIM 10/1

#### Lifetime




Lumen Maintenance Diagram - 13T8-6U/MAS/24-835/IF20/P/DIM 10/1




Life Expectancy Diagram - 13T8-6U/MAS/24-835/IF20/P/DIM 10/1

## MasterClass InstantFit (UL Type-A) T8


#### Lifetime





Life Expectancy Diagram - 13T8-6U/MAS/24-835/IF20/P/DIM 10/1

Life Expectancy Diagram - 13T8-6U/MAS/24-835/IF20/P/DIM 10/1



Lumen Maintenance Diagram - 13T8-6U/MAS/24-835/IF20/P/DIM 10/1



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.