



MasterClass InstantFit (UL Type-A) T8

13T8-6U/MAS/24-840/IF21/P/DIM 10/1

The MasterClass InstantFit T8 lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect. Other lamps claim compatibility but only MasterClass InstantFit (UL Type A) has been proven to work with over 200 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality lamps with no visible flicker and optimized optics. Energy managers will enjoy these lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the MasterClass InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system. With available 70,000 hour life, 7-year limited warranty and a shatter-prevention polycarbonate lens, Philips MasterClass InstantFit TLED lamps deliver benefits for all.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	70,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	840 [CCT of 4000K]

Beam Angle (Nom)	180 degree(s)			
Luminous Flux	2,100 lm			
Color Designation	Cool White (CW)			
Correlated Color Temperature (Nom)	4000 K			
Luminous Efficacy (rated) (Nom)	161.00 lm/W			
Color Consistency	<6			
Color rendering index (CRI)	80			
LLMF At End Of Nominal Lifetime (Nom) 70 %				


Datasheet, 2023, November 3 data subject to change

MasterClass InstantFit (UL Type-A) T8

Operating and Electrical			
Line Frequency	20K to 120K Hz		
Input Frequency	20K to 120K Hz		
Power Consumption	13 W		
Wattage Equivalent	32 W		
Starting Time (Nom)	0.5 s		
Warm-up time to 60% light	0.5 s		
Power Factor (Fraction)	0.9		
Voltage (Nom)	120-277, 347 V		
UL Type	UL Type A		
Temperature			
Ambient temperature range	-4 °F to 113 °F		
T-Case Maximum (Nom)	122 °F		
Controls and Dimming			
Dimmable	Yes		
Mechanical and Housing			
Bulb Finish	Frosted		
Bulb Material	Plastic		
Product Length	23-5/8 inch		
Bulb Shape	Т8		

Approval and Application					
Energy Saving Product	Yes				
Approval Marks	RoHS compliance UL certificate DLC				
	compliance				
Energy Consumption kWh/1000 h	- kWh				
Energy Certifications	DLC Standard				
Application Conditions					
can it be used in closed luminaires	Yes				
Product Data					
Order product name	13T8-6U/MAS/24-840/IF21/P/DIM 10/1				
Full product name	13T8-6U/MAS/24-840/IF21/P/DIM 10/1				
Order code	541870				
Material Nr. (12NC)	929001987604				
Numerator - Quantity Per Pack	1				
EAN/UPC - Product/Case	046677541873				
Numerator - Packs per outer box	10				
EAN/UPC - Case	50046677541878				


Dimensional drawing





Product	D1	D2	A1	A2	A3
13T8-6U/MAS/24-840/	1-1/16 inch	1-1/8 inch	6 inch	22-1/2 inch	1-1/8 inch
IF21/P/DIM 10/1					

MasterClass InstantFit (UL Type-A) T8


Photometric data








Spectral Power Distribution Colour - 13T8-6U/MAS/24-840/IF21/P/DIM 10/1




Calculus/Photometrics 4.5 Philips Lighting B.V. Pager 171

General uniform lighting - 13T8-6U/MAS/24-840/IF21/P/DIM 10/1

Lifetime




Lumen Maintenance Diagram - 13T8-6U/MAS/24-840/IF21/P/DIM 10/1




Life Expectancy Diagram - 13T8-6U/MAS/24-840/IF21/P/DIM 10/1

MasterClass InstantFit (UL Type-A) T8


Lifetime





Life Expectancy Diagram - 13T8-6U/MAS/24-840/IF21/P/DIM 10/1

Life Expectancy Diagram - 13T8-6U/MAS/24-840/IF21/P/DIM 10/1



Lumen Maintenance Diagram - 13T8-6U/MAS/24-840/IF21/P/DIM 10/1



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.