



LED Highbay

75HB/LED/840/ND FB 4/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	8,500 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	113.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	75 W
Lamp Current (Nom)	650 mA
Starting Time (Nom)	0.5 s

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	Type B - bypass the ballast

Temperature	
T-Case Maximum (Nom)	208 °F

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	T-shape

Approval and Application	
Energy Consumption kWh/1000 h	- kWh


Product Data	
Order product name	75HB/LED/840/ND FB 4/1
Full product name	75HB/LED/840/ND FB 4/1
Order code	542324
Material Nr. (12NC)	929001993104

LED Highbay

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677542320
Numerator - Packs per outer box	4


EAN/UPC - Case	50046677542325
----------------	----------------

Dimensional drawing




Product	D	C
75HB/LED/840/ND FB 4/1	5-9/16 inch	10-9/16 inch

Photometric data




Technical Photometric Data Page Lighting ECU Page 1/1



General uniform lighting - 75HB/LED/840/ND FB 4/1


Spectral Power Distribution Colour - 75HB/LED/840/ND FB 4/1




Light Distribution Diagram - 75HB/LED/840/ND FB 4/1

LED Highbay

Lifetime



Lumen Maintenance Diagram - 75HB/LED/840/ND FB 4/1



Life Expectancy Diagram - 75HB/LED/840/ND FB 4/1

