

PHILIPS

Eco passport

38HB/LED/840/ND FB 6/1

LED Highbay

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Available in both plug-and-play (UL Type A) and MainsFit (UL Type B) options, Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.

Energy

- **Dimmable:** No
- **Energy Efficiency Label (EEL):** Not applicable
- **Luminous Efficacy (rated) (Nom):** 100.00 lm/W
- **Power (Rated) (Nom):** 38 W

Circularity

- **Nominal Lifetime (Nom):** 25000 h

Packaging

- **SAP Weight Paper Unit (Case):** 1.020 kg
- **SAP Weight Paper Unit (Piece):** 0.023 kg

Substances

- **EU REACH restrictions compliant:** Yes
- **EU RoHS compliant:** Yes

Weight & Materials

- **Net Weight (Piece):** 0.247 kg

Further reading at:
<https://www.signify.com/global/sustainability/sustainable-lighting>

© 2021 Signify Holding. All rights reserved.