



Standard LED bulbs

LEDBulb 19W E27 6500K W A75 1PF/6 BR

Standard LED bulbs are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving bulbs. They deliver huge energy savings and minimize maintenance costs. The Standard LED bulb is the perfect bulb for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

Product data


General Information			
Cap-Base	E27 [E27]	Lamp Current (Max)	125 mA
Nominal lifetime	25,000 hour(s)	Lamp Current (Min)	75 mA
Switching Cycle	50,000	Wattage Equivalent	110 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.85
		Voltage (Nom)	100-240 V
Light Technical			
Color Code	865 [CCT of 6500K]	Temperature	
Beam Angle (Nom)	150 degree(s)	T-Case Maximum (Nom)	80 °C
Luminous Flux	1,800 lm	Controls and Dimming	
Color Designation	Cool Daylight	Dimmable	No
Correlated Color Temperature (Nom)	6500 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	94.00 lm/W	Bulb Finish	Frosted
Color Consistency	<6	Bulb Shape	A75 [A 75mm]
Color rendering index (CRI)	80	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h	- kWh
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		
Power Consumption	19 W		

Standard LED bulbs

Product Data	
Order product name	LEDBulb 19W E27 6500K W A75 1PF/6 BR
Full product name	LEDBulb 19W E27 6500K W A75 1PF/6 BR
Full product code	871869963977800
Order code	929002003192
Material Nr. (12NC)	929002003192


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699639778
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699639785

Dimensional drawing




Product	D	C
LEDBulb 19W E27 6500K W A75 1PF/6 BR	81 mm	155 mm


Photometric data



Light Distribution Diagram - LEDBulb 19W E27 6500K W A75 1PF/6 BR



Spectral Power Distribution Colour - LEDBulb 19W E27 6500K W A75 1PF/6 BR




General uniform lighting - LEDBulb 19W E27 6500K W A75 1PF/6 BR

Standard LED bulbs

Lifetime



Life Expectancy Diagram - LEDBulb 19W E27 6500K W A75 1PF/6 BR



Lumen Maintenance Diagram - LEDBulb 19W E27 6500K W A75 1PF/6 BR

