



MASTER - LED HID SON-T



TrueForce LED Road 84-55W E40 730

Philips MASTER - LED HID SON-T lamps are an easy LED solution with a short payback period to replace High-Intensity Discharge (HID) and High-Pressure Sodium (SON) lamps. MASTER - LED HID SON-T solutions bring the energy efficiency and long lifetime benefits of LED to HID replacement, providing instant savings for a low initial investment. With the right lamp size and light distribution, you can easily retrofit MASTER - LED HID SON-T lamps into existing SON and SON-T systems, enhancing the lighting quality with LED without changing the luminaire's ballast (for IF replacements) or reflector.

Warnings and Safety

- Please refer to the installation guide or consult a Philips Lighting representative for the wiring diagram and instructions.

Product data


General Information		Operating and Electrical	
Cap-Base	E40	Luminous Efficacy (rated) (Nom)	152.00 lm/W
Nominal lifetime	50,000 hour(s)	Color Consistency	<6
Switching Cycle	50,000	Color rendering index (CRI)	70
Lighting Technology	LED	LLMF At End Of Nominal Lifetime (Nom)	70 %
Flux measurement reference	Sphere	Line Frequency	50 Hz
CE mark	Yes	Input Frequency	50 Hz
EU RoHS compliant	Yes	Power Consumption	55 W
Light Technical		Lamp Current (Nom)	1,000 mA
Color Code	730 [CCT of 3000K]	Starting Time (Nom)	0.5 s
Luminous Flux	8,400 lm	Warm-up time to 60% light	0.5 s
Color Designation	White (WH)	Power Factor (Fraction)	0.9
Correlated Color Temperature (Nom)	3000 K		

MASTER - LED HID SON-T

Voltage (Nom)	88-98 V
Temperature	
T-Case Maximum (Nom)	97 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	Others
Approval and Application	
Energy Efficiency Class	D
Energy Consumption kWh/1000 h	55 kWh


EPREL Registration Number	403607
Product Data	
Order product name	TForce LED Road 84-55W E40 730
Full product name	TrueForce LED Road 84-55W E40 730
Full product code	871869963904400
Order code	63904400
Material Nr. (12NC)	929002007402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699639044
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699639051

Dimensional drawing




Product	D	C
TForce LED Road 84-55W E40 730	71 mm	262 mm

Photometric data




Spectral Power Distribution Colour - TForce LED Road 84-55W E40 730



Light Distribution Diagram - TForce LED Road 84-55W E40 730

MASTER - LED HID SON-T


Photometric data




Technical Parameters 43 Page Lighting E40 Page 117

Accent Lighting Spots - TForce LED Road 84-55W E40 730

Lifetime



Life Expectancy Diagram - TForce LED Road 84-55W E40 730



Lumen Maintenance Diagram - TForce LED Road 84-55W E40 730

