



TrueForce LED Public (Road – SON)

TrueForce LED Road 84-55W E40 730

Philips TrueForce LED road lamps offer an easy and short payback LED solution to replace High Intensity Discharge (HID) lamps. The products bring the energy efficiency and long lifetime benefits of LED to HID replacement and provide instant saving and low initial investment. With the right lamp size and light distribution, you can easily retrofit TrueForce LED road lamps into the existing systems without changing the luminaire's ballast or reflector while enhancing the lighting quality.

Product data


General Information		Power (Rated) (Nom)	
Cap-Base	E40 [E40]		55 W
EU RoHS compliant	Yes	Lamp Current (Nom)	1000 mA
Nominal Lifetime (Nom)	50000 h	Wattage Equivalent	100 W
Switching Cycle	50000X	Starting Time (Nom)	0.5 s
Technical Type	55-100W	Warm Up Time to 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.9
		Voltage (Nom)	88-98 V
Light Technical		Temperature	
Colour Code	730 [CCT of 3000K]	T-Case Maximum (Nom)	97 °C
Luminous Flux (Nom)	8400 lm		
Colour Designation	White (WH)	Controls and Dimming	
Colour Temperature, horizontal (Nom)	3000 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	152.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Colour Rendering Index horiz (Nom)	70	Bulb Finish	Clear
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical		Approval and Application	
Input Frequency	50 Hz	Energy Efficiency Label	A++

TrueForce LED Public (Road – SON)

Energy Consumption kWh/1000 h	61 kWh
Product Data	
Full product code	871869963904400
Order product name	TrueForce LED Road 84-55W E40 730
EAN/UPC - Product	8718699639044
Order code	63904400

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002007402
Net Weight (Piece)	0.432 kg


Dimensional drawing




TForce LED SON-T ND 8.5klm E40 730 CL

Product	D	C
TrueForce LED Road 84-55W E40 730	71 mm	262 mm


Photometric data



LEDTrueForce SON-T 85klm E40 730





LEDTrueForce SON-T E40 55W



LEDTrueForce SON-T 85klm E40 730

TrueForce LED Public (Road – SON)

Lifetime



LEDTrueForce SON-T E40

LEDTrueForce SON-T E40

