

PHILIPS

Eco passport

TrueForce LED Road 120-68W E40 740 TrueForce LED Public (Road – SON)

Philips TrueForce LED road lamps offer an easy and short payback LED solution to replace High Intensity Discharge (HID) lamps. The products bring the energy-efficiency and long lifetime benefits of LED to HID replacement and provide instant saving and low initial investment. With the right lamp size and light distribution, you can easily retrofit TrueForce LED road lamps into the existing systems without changing the luminaire's ballast or reflector while enhancing the lighting quality.

Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



Energy

- **Dimmable:** No
- **Energy efficiency label (EEL):** A++
- **Lamp Luminous Efficacy EM (Nom):** 176.00 lm/W
- **Power (Rated) (Nom):** 68 W



Circularity

- **Nominal lifetime (nom.):** 50000 h



Packaging

- **SAP Weight Paper Unit (Case):** 1.408 kg
- **SAP Weight Paper Unit (Piece):** 0.068 kg



Substances

- **EU RoHS compliant:** Yes



Weight & Materials

- **Net Weight (Piece):** 0.432 kg

Energy efficiency ranking / External awards



Further reading at:

<https://www.philips.com/a-w/about/sustainability/sustainable-planet/green-products-and-green-innovation.html>

© 2021 Signify Holding. All rights reserved.