



T8

9.5T8/MAS/48-830/IF15/P/DIM 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

General Information					
Cap-Base	G13 [Medium Bi-Pin Fluorescent]				
Nominal lifetime	70,000 hour(s)				
Switching Cycle	50,000				
Lighting Technology	LED				
EU RoHS compliant	Yes				
Light Technical					
Color Code	830 [CCT of 3000K]				
Beam Angle (Nom)	180 degree(s)				
Luminous Flux	1,500 lm				
Color Designation	White (WH)				
Correlated Color Temperature (Nom)	3000 K				
Luminous Efficacy (rated) (Nom)	157.00 lm/W				
Color Consistency	<6				
Color rendering index (CRI)	80				
LLMF At End Of Nominal Lifetime (Nom)	70 %				
Operating and Electrical					
Line Frequency	50 to 60 Hz				


Input Frequency	50 to 60 Hz			
Power Consumption	9.5 W			
Starting Time (Nom)	0.5 s			
Warm-up time to 60% light	0.5 s			
Power Factor (Fraction)	0.9			
Voltage (Nom)	120-277, 347 V			
UL Type	Type A - works on ballast			
Temperature				
Ambient temperature range	-20 °C to 55 °C			
T-Case Maximum (Nom)	55 ℃			
Controls and Dimming				
Dimmable	Yes			
Mechanical and Housing				
Bulb Finish	Frosted			
Bulb Material	Plastic			
Product Length	1,200 mm			

Datasheet, 2023, May 15 data subject to change

Bulb Shape	Т8			
Approval and Application				
Energy Saving Product	Yes			
Approval Marks	RoHS compliance UL certificate			
Energy Consumption kWh/1000 h	- kWh			
Product Data				
Order product name	9.5T8/MAS/48-830/IF15/P/DIM 10/1			


Full product name	9.5T8/MAS/48-830/IF15/P/DIM 10/1
Order code	473974
Material Nr. (12NC)	929002015804
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677473976
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677473971

Dimensional drawing



Product	D1	D2	A1	A2	А3
9.5T8/MAS/48-830/IF15/P/DIM	25.7 mm	28 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
10/1					


Photometric data






Spectral Power Distribution Colour - 9.5T8/MAS/48-830/IF15/P/DIM 10/1







Light Distribution Diagram - 9.5T8/MAS/48-830/IF15/P/DIM 10/1

Lifetime






Life Expectancy Diagram - 9.5T8/MAS/48-830/IF15/P/DIM 10/1








Life Expectancy Diagram - 9.5T8/MAS/48-830/IF15/P/DIM 10/1

Life Expectancy Diagram - 9.5T8/MAS/48-830/IF15/P/DIM 10/1





Lumen Maintenance Diagram - 9.5T8/MAS/48-830/IF15/P/DIM 10/1



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.