

# PHILIPS

# MasterClass InstantFit (UL Type-A) T8

### 15.5T8/MAS/48-835/IF24/P/DIM 25/1

The MasterClass InstantFit T8 lamps provide hassle-free installation with simple lamp-for-lamp replacements. They deliver what we promise, with at least 40% energy savings, flicker-free performance, and the life you would expect. Other lamps claim compatibility but only MasterClass InstantFit (UL Type A) has been proven to work with over 200 ballasts and drivers, delivering even light output, with proven energy savings and a long average lifetime. End users will be delighted being under these comfortable and high quality lamps with no visible flicker and optimized optics. Energy managers will enjoy these lamps too as they can count the savings delivered by our lamps. To enjoy more energy savings, the MasterClass InstantFit lamps can be paired with the Advance TLED drivers to create a Type C system. With available 70,000 hour life, 7-year limited warranty and a shatter-prevention polycarbonate lens, Philips MasterClass InstantFit TLED lamps deliver benefits for all.

#### **Product data**

General Information				
Cap-Base	G13 [Medium Bi-Pin Fluorescent]			
Nominal lifetime	70,000 hour(s)			
Switching Cycle	50,000			
Lighting Technology	LED			
EU RoHS compliant	Yes			
Light Technical				
Color Code	835 [CCT of 3500K]			

Beam Angle (Nom)	180 degree(s)			
Luminous Flux	2,400 lm			
Color Designation	White (WH)			
Correlated Color Temperature (Nom)	3500 K			
Luminous Efficacy (rated) (Nom)	154 lm/W			
Color Consistency	<6			
Color rendering index (CRI)	80			
LLMF At End Of Nominal Lifetime (Nom) 70 %				


Datasheet, 2023, November 3 data subject to change

# MasterClass InstantFit (UL Type-A) T8

Operating and Electrical					
Line Frequency	20K to 120K Hz				
Input Frequency	20K to 120K Hz				
Power Consumption	15.5 W				
Lamp Current (Max)	320 mA				
Lamp Current (Min)	60 mA				
Wattage Equivalent	32 W				
Starting Time (Nom)	0.5 s				
Warm-up time to 60% light	0.5 s				
Power Factor (Fraction)	0.9				
Voltage (Nom)	120-277,347 V				
UL Type	UL Type A				
Temperature					
Ambient temperature range	-4 °F to 131 °F				
T-Case Maximum (Nom)	104 °F				
Controls and Dimming					
Dimmable	Only with specific dimmers				
Mechanical and Housing					
Bulb Finish	Frosted				
Bulb Material	Plastic				

Product Length	47-1/4 inch		
Bulb Shape	T8		
Approval and Application			
Energy Saving Product	Yes		
Approval Marks	RoHS compliance UL certificate DLC		
	compliance		
Energy Consumption kWh/1000 h	- kWh		
Application Conditions			
can it be used in closed luminaires	Yes		
Product Data			
Order product name	15.5T8/MAS/48-835/IF24/P/DIM 25/1		
Full product name	15.5T8/MAS/48-835/IF24/P/DIM 25/1		
Order code	533372		
Material Nr. (12NC)	929002016304		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	046677545185		
Numerator - Packs per outer box	25		
EAN/UPC - Case	50046677545180		


# Dimensional drawing




Product	D1	D2	A1	A2	А3
15.5T8/MAS/48-835/	1-1/16 inch	1-1/8 inch	47-3/16 inch	47-1/2 inch	47-3/4 inch
IF24/P/DIM 25/1					

# MasterClass InstantFit (UL Type-A) T8


#### Photometric data








Spectral Power Distribution Colour - 15.5T8/MAS/48-835/IF24/P/DIM 25/1




Calculus Photometria 4.5 Philips Lighting B.V. Page: 171

General uniform lighting - 15.5T8/MAS/48-835/IF24/P/DIM 25/1

#### Lifetime




Lumen Maintenance Diagram - 15.5T8/MAS/48-835/IF24/P/DIM 25/1




Life Expectancy Diagram - 15.5T8/MAS/48-835/IF24/P/DIM 25/1

# MasterClass InstantFit (UL Type-A) T8


#### Lifetime





Life Expectancy Diagram - 15.5T8/MAS/48-835/IF24/P/DIM 25/1

Lumen Maintenance Diagram - 15.5T8/MAS/48-835/IF24/P/DIM 25/1



Life Expectancy Diagram - 15.5T8/MAS/48-835/IF24/P/DIM 25/1



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.