



MASTER LEDtube EM/ Mains T8

MAS LEDtube 1200mm UO 15.5W 865 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

Warnings and Safety

- -
- -

Product data

General Information	
Cap-Base	G13 ROT (Rotating) [Medium Bi-Pin Fluorescent]
Nominal lifetime	60,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	2,500 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	161.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	83


LLMF At End Of Nominal Lifetime (Nom) 70 %	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	15.5 W
Lamp Current (Max)	73 mA
Lamp Current (Min)	67 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	55 °C

MASTER LEDtube EM/Mains T8

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Material	Plastic
Product Length	1,200 mm
Bulb Shape	T8
Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance TUV CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	16 kWh



Product Data	
Order product name	MAS LEDtube 1200mm UO 15.5W 865 T8
Full product name	MAS LEDtube 1200mm UO 15.5W 865 T8
Full product code	871869964725400
Order code	929002020702
Material Nr. (12NC)	929002020702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699647254
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699647261

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 1200mm UO 15.5W 865 T8	25.8 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

Photometric data




Accent Lighting Spots - MAS LEDtube 1200mm UO 15.5W 865 T8

Light Distribution Diagram - MAS LEDtube 1200mm UO 15.5W 865 T8


MASTER LEDtube EM/Mains T8

Photometric data




Spectral Power Distribution Colour - MAS LEDtube 1200mm UO 15.5W 865 T8


Lifetime




Life Expectancy Diagram - MAS LEDtube 1200mm UO 15.5W 865 T8



Lumen Maintenance Diagram - MAS LEDtube 1200mm UO 15.5W 865 T8




Life Expectancy Diagram - MAS LEDtube 1200mm UO 15.5W 865 T8



Lumen Maintenance Diagram - MAS LEDtube 1200mm UO 15.5W 865 T8

MASTER LEDtube EM/Mains T8

Lifetime



Life Expectancy Diagram - MAS LEDtube 1200mm UO 15.5W 865 T8

