

## MASTER LEDtube VLE 1500mm HO 20.5W 840 T8 MASTER Value LEDtube T8

A high-performance LED solution, the professional MASTER Value LED tube is ideal for replacing T8 fluorescent lamps using EM ballast or installing directly on the mains. This product provides an optimal combination of value and performance – for use in all general lighting, office, industry, retail, and hospitality applications. The unique design of this LED T8 tube light offers wide compatibility, safety and fast installation, as well as instant energy savings.



### Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process, we innovate to reduce our environmental impact by taking climate action and by focusing on circularity and bring wider benefits to the world we operate in via social aspects as food availability, health & wellbeing, and safety & security.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



#### Energy

- **Dimmable:** No
- **Energy Efficiency Class:** D
- **Luminous Efficacy (rated) (Nom):** 151 lm/W
- **Power (Rated) (Nom):** 20.5 W



#### Circularity

- **Nominal Lifetime (Nom):** 60000 h



#### Packaging

- **Copy SAP Weight Paper Unit (Case):** 1.161 kg
- **Copy SAP Weight Paper Unit (Piece):** 0.058 kg



#### Substances

- **EU REACH restrictions compliant:** Yes
- **EU REACH SVHC declaration:** Yes
- **EU RoHS compliant:** Yes



#### Weight & Materials

- **Copy Net Weight (Piece):** 0.275 kg

#### Energy efficiency ranking / External awards

