



MASTER Value LEDtube T8

MASTER LEDtube VLE 1500mm UO 24W 865 T8

A high-performance LED solution, the professional MASTER Value LED tube is ideal for replacing T8 fluorescent lamps using EM ballast or installing directly on the mains. This product provides an optimal combination of value and performance – for use in all general lighting, office, industry, retail, and hospitality applications. The unique design of this LED T8 tube light offers wide compatibility, safety and fast installation, as well as instant energy savings.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	3,700 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	154.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	24 W
Lamp Current (Max)	112 mA
Lamp Current (Min)	103 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No

MASTER Value LEDtube T8


Mechanical and Housing	
Bulb Material	Glass
Product Length	1,500 mm
Bulb Shape	T8

Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance TUV CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	24 kWh

Product Data	
Order product name	MAS LEDtube VLE 1500mm UO 24W 865 T8


Full product name	MASTER LEDtube VLE 1500mm UO 24W 865 T8
Full product code	871869964707000
Order code	64707000
Material Nr. (12NC)	929002022502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699647070
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699647087

Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube VLE 1500mm UO 24W 865 T8	25.8 mm	28 mm	1,498.7 mm	1,505.8 mm	1,512.9 mm

Photometric data




Light Distribution Diagram - MAS LEDtube VLE 1500mm UO 24W 865 T8



Spectral Power Distribution Colour - MAS LEDtube VLE 1500mm UO 24W 865 T8

MASTER Value LEDtube T8


Photometric data




General uniform lighting - MAS LEDtube VLE 1500mm UO 24W 865 T8

General uniform lighting - MAS LEDtube VLE 1500mm UO 24W 865 T8


Lifetime




Lumen Maintenance Diagram - MAS LEDtube VLE 1500mm UO 24W 865 T8



Lumen Maintenance Diagram - MAS LEDtube VLE 1500mm UO 24W 865 T8




Life Expectancy Diagram - MAS LEDtube VLE 1500mm UO 24W 865 T8



Life Expectancy Diagram - MAS LEDtube VLE 1500mm UO 24W 865 T8

MASTER Value LEDtube T8

Lifetime



Life Expectancy Diagram - MAS LEDtube VLE 1500mm UO 24W 865 T8

