



# LED BR30

## 7.2BR30/PER/940/P/E26/DIM 6/1FB T20

Philips BR30 LED lamps are the smart alternative to standard incandescent. The traditional lamp design can provide excellent dimming performance with spectacular energy savings. They provide the beautiful light and dependable performance you expect from LED at an economical price.

### Product data


General Information	
Cap-Base	E26 [ Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	7.2-65W
Light Technical	
Color Code	940 [ CCT of 4000K]
Beam Angle (Nom)	90 °
Luminous Flux (Nom)	650 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Nom)	7.2 W
Lamp Current (Nom)	82 mA
Wattage Equivalent	65 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	BR-30 (BR30)
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	7.2BR30/PER/940/P/E26/DIM 6/1FB T20
EAN/UPC - Product	046677545918
Order code	929002032204
Numerator - Quantity Per Pack	1

# LED BR30

Numerator - Packs per outer box	6
Material Nr. (12NC)	929002032204
Net Weight (Piece)	0.095 kg


## Dimensional drawing




BR30 120V 7.2-65W 650lm 4000K E26 D

Product	D	C
7.2BR30/PER/940/P/E26/DIM 6/1FB T20	95 mm	132 mm


## Photometric data



LEDBulbs\_BR30 120V 72-65W 650lm 3000K E26 D





LEDBulbs\_BR30 120V 72-65W 650lm 4000K E26 D



LEDBulbs\_BR30 120V 72-65W 650lm 4000K E26 D

# LED BR30

## Lifetime



LEDBulbs BR30 120V 19-120W 1200lm 2700K E26 D

LEDBulbs BR30 120V 19-120W 1200lm 2700K E26 D

