

8.8BR40/PER/930/P/E26/DIM 6/1FB T20LED BR40

Philips BR40 LED lamps are the smart alternative to standard incandescent. The traditional lamp design can provide excellent dimming performance with spectular energy savings. They provide the beautiful light and dependable performance you expect from LED at an economical price.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process, we innovate to reduce our environmental impact by taking climate action and by focusing on circularity and bring wider benefits to the world we operate in via social aspects as food availability, health & wellbeing, and safety & security.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



- Dimmable: Yes
- Luminous Efficacy (rated) (Nom): 90.00 lm/W
- Power (Rated) (Nom): 8.8 W

Circularity

• Nominal Lifetime (Nom): 15000 h



- Copy SAP Weight Paper Unit (Case): 1.552 lb
- Copy SAP Weight Paper Unit (Piece): 0.159 lb



- EU REACH restrictions compliant: Yes
- EU REACH SVHC declaration: Yes
- EU RoHS compliant: Yes



Weight & Materials

• Copy Net Weight (Piece): 0.364 lb