

CorePro Plastic (Dimmable) A-Shape Lamps

5A19/PER/930/P/E26/DIM 6/1FB T20

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	250 degree(s)
Luminous Flux	450 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	5 W
Lamp Current (Nom)	55 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	167 °F

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19


CorePro Plastic (Dimmable) A-Shape Lamps

Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star

Product Data	
Order product name	5A19/PER/930/P/E26/DIM 6/1FB T20
Full product name	5A19/PER/930/P/E26/DIM 6/1FB T20
Order code	550418


Material Nr. (12NC)	929002035804
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677550417
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677550412

Dimensional drawing




Product	D	C
5A19/PER/930/P/E26/DIM 6/1FB T20	2-1/2 inch	4-7/16 inch


Photometric data



Spectral Power Distribution Colour - 5A19/PER/930/P/E26/DIM 6/1FB T20




Light Distribution Diagram - 5A19/PER/930/P/E26/DIM 6/1FB T20




General uniform lighting - 5A19/PER/930/P/E26/DIM 6/1FB T20

CorePro Plastic (Dimmable) A-Shape Lamps

Lifetime



Life Expectancy Diagram - 5A19/PER/930/P/E26/DIM 6/1FB T20



Lumen Maintenance Diagram - 5A19/PER/930/P/E26/DIM 6/1FB T20

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.