


# CorePro Plastic (Dimmable) A-Shape Lamps

## 5A19/PER/950/P/E26/DIM 6/1FB T20

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

### Product data

| General Information | |
|---|---|
| **Cap-Base** | E26 [Single Contact Medium Screw] |
| **Nominal lifetime** | 15,000 hour(s) |
| **Switching Cycle** | 50,000 |
| **Lighting Technology** | LED |
| **EU RoHS compliant** | Yes |

| Light Technical | |
|---|---|
| **Color Code** | 950 [CCT of 5000K] |
| **Beam Angle (Nom)** | 250 degree(s) |
| **Luminous Flux** | 450 lm |
| **Color Designation** | Daylight |
| **Correlated Color Temperature (Nom)** | 5000 K |
| **Luminous Efficacy (rated) (Nom)** | 90.00 lm/W |
| **Color Consistency** | <4 |
| **Color rendering index (CRI)** | 90 |
| **LLMF At End Of Nominal Lifetime (Nom)** | 70 % |

| Operating and Electrical | |
|---|---|
| **Line Frequency** | 60 Hz |
| **Input Frequency** | 60 Hz |
| **Power Consumption** | 5 W |
| **Lamp Current (Nom)** | 55 mA |
| **Wattage Equivalent** | 40 W |
| **Starting Time (Nom)** | 0.5 s |
| **Warm-up time to 60% light** | 0.5 s |
| **Power Factor (Fraction)** | 0.7 |
| **Voltage (Nom)** | 120 V |

| Temperature | |
|---|---|
| **T-Case Maximum (Nom)** | 167 °F |

| Controls and Dimming | |
|---|---|
| **Dimmable** | Yes |

| Mechanical and Housing | |
|---|---|
| **Bulb Finish** | Frosted |
| **Bulb Material** | Plastic |
| **Bulb Shape** | A19 [A 19mm] |


# CorePro Plastic (Dimmable) A-Shape Lamps

| Approval and Application | |
|---|---|
| **Energy Consumption kWh/1000 h** | - kWh |
| **Energy Certifications** | Energy Star |

| Product Data | |
|---|---|
| **Order product name** | 5A19/PER/950/P/E26/DIM 6/1FB T20 |
| **Full product name** | 5A19/PER/950/P/E26/DIM 6/1FB T20 |
| **Order code** | 550426 |


| | |
|---|---|
| **Material Nr. (12NC)** | 929002036004 |
| **Numerator - Quantity Per Pack** | 1 |
| **EAN/UPC - Product/Case** | 046677550424 |
| **Numerator - Packs per outer box** | 6 |
| **EAN/UPC - Case** | 50046677550429 |

## Dimensional drawing





| Product | D | C |
|---|---|---|
| 5A19/PER/950/P/E26/DIM 6/1FB T20 | 2-1/2 inch | 4-7/16 inch |


## Photometric data




General uniform lighting - 5A19/PER/950/P/E26/DIM 6/1FB T20





Light Distribution Diagram - 5A19/PER/950/P/E26/DIM 6/1FB T20





Spectral Power Distribution Colour - 5A19/PER/950/P/E26/DIM 6/1FB T20

# CorePro Plastic (Dimmable) A-Shape Lamps

## Lifetime




Life Expectancy Diagram - 5A19/PER/950/P/E26/DIM 6/1FB T20




Lumen Maintenance Diagram - 5A19/PER/950/P/E26/DIM 6/1FB T20

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.