



CorePro Plastic (Dimmable) A-Shape Lamps

8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

Product data

| General Information | | | |
|---------------------------------------|-----------------------------------|---------------------------|---------|
| Cap-Base | E26 [Single Contact Medium Screw] | Input Frequency | 60 Hz |
| Nominal lifetime | 15,000 hour(s) | Power Consumption | 8.8 W |
| Switching Cycle | 50,000 | Lamp Current (Nom) | 80 mA |
| Lighting Technology | LED | Wattage Equivalent | 60 W |
| EU RoHS compliant | Yes | Starting Time (Nom) | 0.5 s |
| | | Warm-up time to 60% light | 0.5 s |
| | | Power Factor (Fraction) | 0.7 |
| | | Voltage (Nom) | 120 V |
| Light Technical | | Temperature | |
| Color Code | 927 | T-Case Maximum (Nom) | 194 °F |
| Beam Angle (Nom) | 250 degree(s) | | |
| Luminous Flux | 800 lm | Controls and Dimming | |
| Color Designation | Warm White (WW) | Dimmable | Yes |
| Correlated Color Temperature (Nom) | 2700 K | | |
| Luminous Efficacy (rated) (Nom) | 90.00 lm/W | Mechanical and Housing | |
| Color Consistency | <4 | Bulb Finish | Frosted |
| Color rendering index (CRI) | 90 | Bulb Material | Plastic |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % | Bulb Shape | A19 |
| Operating and Electrical | | | |
| Line Frequency | 60 Hz | | |

CorePro Plastic (Dimmable) A-Shape Lamps

| UL Wet/ damp/ dry location | Damp location |
|----------------------------|---------------|
|----------------------------|---------------|

Approval and Application

| | |
|-------------------------------|-------|
| Energy Consumption kWh/1000 h | - kWh |
|-------------------------------|-------|

| | |
|-----------------------|-------------|
| Energy Certifications | Energy Star |
|-----------------------|-------------|

| | |
|---------------|-----|
| T20 compliant | Yes |
|---------------|-----|

Application Conditions

| | |
|-------------------------------------|-----|
| can it be used in closed luminaires | Yes |
|-------------------------------------|-----|

Product Data

| | |
|--------------------|---------------------------------------|
| Order product name | 8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT |
|--------------------|---------------------------------------|

| | |
|-------------------|---------------------------------------|
| Full product name | 8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT |
|-------------------|---------------------------------------|

| | |
|------------|--------|
| Order code | 550434 |
|------------|--------|

| | |
|---------------------|--------------|
| Material Nr. (12NC) | 929002036104 |
|---------------------|--------------|


| | |
|-------------------------------|---|
| Numerator - Quantity Per Pack | 1 |
|-------------------------------|---|

| | |
|------------------------|--------------|
| EAN/UPC - Product/Case | 046677550431 |
|------------------------|--------------|

| | |
|---------------------------------|---|
| Numerator - Packs per outer box | 6 |
|---------------------------------|---|


| | |
|----------------|----------------|
| EAN/UPC - Case | 50046677550436 |
|----------------|----------------|

Dimensional drawing




| Product | D | C |
|---------------------------------------|------------|-------------|
| 8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT | 2-1/2 inch | 4-7/16 inch |

Photometric data




General uniform lighting - 8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT



**Spectral Power Distribution Colour - 8.8A19/COR/927/FR/P/E26/DIM/T20
6/1CT**

CorePro Plastic (Dimmable) A-Shape Lamps

Photometric data




Light Distribution Diagram - 8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT

Lifetime



Life Expectancy Diagram - 8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT



Lumen Maintenance Diagram - 8.8A19/COR/927/FR/P/E26/DIM/T20 6/1CT

