



# CorePro Plastic (Dimmable) A-Shape Lamps

## 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

Dimmable A-shape lamps that offer over 25,000 hours lifetime. Title 20 listed lamps that can be sold in California and ideal for commercial spaces nationwide.

### Product data


<b>General Information</b>		<b>Input Frequency</b>		60 Hz
Cap-Base	E26 [Single Contact Medium Screw]	Power Consumption	8.8 W	
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	80 mA	
Switching Cycle	50,000	Wattage Equivalent	60 W	
Lighting Technology	LED	Starting Time (Nom)	0.5 s	
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s	
		Power Factor (Fraction)	0.7	
<b>Light Technical</b>		Voltage (Nom)	120 V	
Color Code	930 [CCT of 3000K]			
Beam Angle (Nom)	250 degree(s)	<b>Temperature</b>		
Luminous Flux	800 lm	T-Case Maximum (Nom)	194 °F	
Color Designation	White (WH)			
Correlated Color Temperature (Nom)	3000 K	<b>Controls and Dimming</b>		
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Dimmable	Yes	
Color Consistency	<4			
Color rendering index (CRI)	90	<b>Mechanical and Housing</b>		
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Finish	Frosted	
		Bulb Material	Plastic	
<b>Operating and Electrical</b>		Bulb Shape	A19	
Line Frequency	60 Hz			

CorePro Plastic (Dimmable) A-Shape Lamps

UL Wet/ damp/ dry location	Damp location
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star
T20 compliant	Yes
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT


Full product name	8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT
Order code	550442
Material Nr. (12NC)	929002036204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677550448
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677550443

Dimensional drawing




Product	D	C
8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT	2-1/2 inch	4-7/16 inch

Photometric data




Light Distribution Diagram - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT



General uniform lighting - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

# CorePro Plastic (Dimmable) A-Shape Lamps

## Photometric data




Spectral Power Distribution Colour - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

## Lifetime



Life Expectancy Diagram - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT



Lumen Maintenance Diagram - 8.8A19/COR/930/FR/P/E26/DIM/T20 6/1CT

