



LED BR30

7.2BR30/PER/950/P/E26/DIM 6/1FB T20

Philips BR30 LED lamps are the smart alternative to standard incandescent. The traditional lamp design can provide excellent dimming performance with spectacular energy savings. They provide the beautiful light and dependable performance you expect from LED at an economical price.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	7.2-65W
Light Technical	
Color Code	950 [CCT of 5000K]
Beam Angle (Nom)	110 °
Initial lumen (Nom)	650 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	7.2 W
Lamp Current (Nom)	82 mA
Wattage Equivalent	65 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Product Data	
Order product name	7.2BR30/PER/950/P/E26/DIM 6/1FB T20
EAN/UPC - Product	046677548100
Order code	548107
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002204163
Net Weight (Piece)	0.095 kg


LED BR30

Dimensional drawing


Product	D	C
7.2BR30/PER/950/P/E26/DIM 6/1FB T20	95 mm	132 mm

BR30 7.2-65W 650lm 5000K E26 D

Photometric data




© 2020 Philips Lighting B.V. Page 1/11



LEDbulb 65W E26 BR30 950 Frosted


LEDbulb 45,65W E26 930 Frosted



LEDbulb 65W E26 BR30 950 Frosted

LED BR30

Lifetime



15K LED

15K LMP

