



LED G25

5.5G25/PER/950/FR/G/E26/DIM 1FBT20

Philips G25 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	950 [CCT of 5000K]
Luminous Flux	500 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	0.7 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	5.5 W
Lamp Current (Nom)	60 mA
Wattage Equivalent	60 W

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	60 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Bulb Shape	G25 (G25)

Approval and Application	
Energy Consumption kWh/1000 h	- kWh
EyeComfort	Yes

Product Data	
Order product name	5.5G25/PER/950/FR/G/E26/DIM 1FBT20
Full product name	5.5G25/PER/950/FR/G/E26/DIM 1FBT20
Order code	929002207004

LED G25



Material Nr. (12NC)	929002207004
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677549213
Numerator - Packs per outer box	10

EAN/UPC - Case	50046677549218
----------------	----------------

Dimensional drawing


Product	D	C
5.5G25/PER/950/FR/G/E26/DIM 1FBT20	80 mm	111 mm

Photometric data



General uniform lighting - 5.5G25/PER/950/FR/G/E26/DIM 1FBT20

Light Distribution Diagram - 5.5G25/PER/950/FR/G/E26/DIM 1FBT20




Spectral Power Distribution Colour - 5.5G25/PER/950/FR/G/E26/DIM 1FBT20

LED G25

Lifetime



Life Expectancy Diagram - 5.5G25/PER/950/FR/G/E26/DIM 1FBT20



Lumen Maintenance Diagram - 5.5G25/PER/950/FR/G/E26/DIM 1FBT20

