



LED A15

3.8A15/PER/927-922/CL/G/E12/WGX1FB T20

Philips A15 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data


General Information		Starting Time (Nom)		0.5 s
Cap-Base	E12 [Candelabra Screw]	Warm-up time to 60% light		0.5 s
Nominal lifetime	15,000 hour(s)	Power Factor (Fraction)		0.75
Switching Cycle	20,000	Voltage (Nom)		120 V
Rated Lifetime (Hours)	15,000 hour(s)	Temperature		
Lighting Technology	LED	T-Case Maximum (Nom)		122 °F
EU RoHS compliant	Yes	Controls and Dimming		
Light Technical		Dimmable		
Color Code	927-922 [CCT of 2700K-2200K]	Yes		
Luminous Flux	350 lm	Mechanical and Housing		
Color Designation	Warm Glow(WG)	Bulb Finish		
Correlated Color Temperature (Nom)	2700 2200 K	Clear		
Luminous Efficacy (rated) (Nom)	92.00 lm/W	Bulb Material		
Color Consistency	<4	Glass		
Color rendering index (CRI)	90	Bulb Shape		
LLMF At End Of Nominal Lifetime (Nom)	70 %	A15 [A 15mm]		
Operating and Electrical		Approval and Application		
Line Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h		
Input Frequency	50 to 60 Hz	- kWh		
Power Consumption	3.8 W	EyeComfort		
Lamp Current (Nom)	42 mA	Yes		
Wattage Equivalent	40 W	Product Data		
		Order product name		
		3.8A15/PER/927-922/CL/G/E12/WGX1FB T20		
		Full product name		
		3.8A15/PER/927-922/CL/G/E12/WGX1FB T20		
		Order code		
		549378		

LED A15

Material Nr. (12NC)	929002208104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677549374
Numerator - Packs per outer box	10


EAN/UPC - Case	50046677549379
----------------	----------------

Dimensional drawing




Product	D	C
3.8A15/PER/927-922/CL/G/E12/WGX1FB T20	1-7/8 inch	3-5/8 inch


Photometric data



Spectral Power Distribution Colour - 3.8A15/PER/927-922/CL/G/E12/WGX1FB T20



Light Distribution Diagram - 3.8A15/PER/927-922/CL/G/E12/WGX1FB T20



LED A15

Lifetime



Life Expectancy Diagram - 3.8A15/PER/927-922/CL/G/E12/WGX1FB T20



Lumen Maintenance Diagram - 3.8A15/PER/927-922/CL/G/E12/WGX1FB T20

