



A-Shape LED

8.8A19/LED/927/P/E26/ND 6/1FB T20

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	11,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	927
Beam Angle (Nom)	210 degree(s)
Luminous Flux	800 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	8.8 W
Lamp Current (Nom)	105 mA
Wattage Equivalent	60 W


Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	212 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19 [A 19mm]
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	8.8A19/LED/927/P/E26/ND 6/1FB T20
Full product name	8.8A19/LED/927/P/E26/ND 6/1FB T20
Order code	554428
Material Nr. (12NC)	929002227204

A-Shape LED

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677554422
Numerator - Packs per outer box	6


EAN/UPC - Case	50046677554427
----------------	----------------

Dimensional drawing




Product	D	C
8.8A19/LED/927/P/E26/ND 6/1FB T20	2-7/16 inch	4-7/16 inch

Photometric data




Technical Parameters 41 Page Lighting 41 Page 177




Technical Parameters 41 Page Lighting 41 Page 177

Accent Lighting Spots - 8.8A19/LED/927/P/E26/ND 6/1FB T20



Light Distribution Diagram - 8.8A19/LED/927/P/E26/ND 6/1FB T20

General uniform lighting - 8.8A19/LED/927/P/E26/ND 6/1FB T20



Spectral Power Distribution Colour - 8.8A19/LED/927/P/E26/ND 6/1FB T20

A-Shape LED

Lifetime



Life Expectancy Diagram - 8.8A19/LED/927/P/E26/ND 6/1FB T20



Lumen Maintenance Diagram - 8.8A19/LED/927/P/E26/ND 6/1FB T20

