



# A-Shape LED

## 8.8A19/LED/950/P/E26/ND 6/1FB T20

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	11,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	950 [CCT of 5000K]
Beam Angle (Nom)	210 degree(s)
Luminous Flux	800 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	8.8 W
Lamp Current (Nom)	105 mA
Wattage Equivalent	60 W

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	212 °F

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19 [A 19mm]

Approval and Application	
Energy Consumption kWh/1000 h	- kWh


Product Data	
Order product name	8.8A19/LED/950/P/E26/ND 6/1FB T20
Full product name	8.8A19/LED/950/P/E26/ND 6/1FB T20
Order code	554444
Material Nr. (12NC)	929002227304

A-Shape LED

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677554446
Numerator - Packs per outer box	6



EAN/UPC - Case	50046677554441
----------------	----------------

Dimensional drawing




Product	D	C
8.8A19/LED/950/P/E26/ND 6/1FB T20	2-7/16 inch	4-7/16 inch

Photometric data




Spectral Power Distribution Colour - 8.8A19/LED/950/P/E26/ND 6/1FB T20



Light Distribution Diagram - 8.8A19/LED/950/P/E26/ND 6/1FB T20

General uniform lighting - 8.8A19/LED/950/P/E26/ND 6/1FB T20



Accent Lighting Spots - 8.8A19/LED/950/P/E26/ND 6/1FB T20

A-Shape LED

Lifetime



Life Expectancy Diagram - 8.8A19/LED/950/P/E26/ND 6/1FB T20



Lumen Maintenance Diagram - 8.8A19/LED/950/P/E26/ND 6/1FB T20

