



LED A19-A21

16.6A21/LED/927/P/E26/ND 6/1FB T20

Philips A19/A21 LED lamps are the smart alternative to standard incandescent. The unique lamp design provides omni-directional light with excellent dimming performance.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	11000 h
Switching Cycle	50000X
Technical Type	16.6-100W

Light Technical	
Color Code	927
Beam Angle (Nom)	210 °
Initial lumen (Nom)	1500 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	16.6 W
Lamp Current (Nom)	145 mA
Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	100 °C


Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted

Product Data	
Order product name	16.6A21/LED/927/P/E26/ND 6/1FB T20
EAN/UPC - Product	046677554460
Order code	554469
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002227604
Net Weight (Piece)	0.174 kg

LED A19-A21


Dimensional drawing




A21 120V 16.6-100W 1500lm 2700K E26 D

Product	D	C
16.6A21/LED/927/P/E26/ND 6/1FB T20	77.5 mm	139.5 mm



Photometric data



Bulb A19 120V 8 8-60W 800lm 2700K E26 D



A21 120V 16 6-100W 1500lm 2700K E26 D





A21 120V 16 6-100W 1500lm 2700K E26 D

A21_120V_16.6-100W_1500lm_2700K_E26_D

LED A19-A21

Lifetime



Bulb A19 120V 8 8-60W 800lm 2700K E26 D

Bulb A19 120V 8 8-60W 800lm 2700K E26 D

