



LED Corn Cobs

63CC/LED/830/ND EX39 BB 6/1

Philips Corn Cob LED replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Product data

General Information	
Base	EX39 [Exclusionary Mogul Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	63-175W

Light Technical	
Color Code	830 [CCT of 3000K]
Initial lumen (Nom)	8400 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	133.00 lm/W
Color Consistency	ANSI 3000K quadrangle
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	63 W
Wattage Equivalent	175 W
Starting Time (Nom)	2.5 s
Warm Up Time to 60% Light (Nom)	2.5 s

UL Type	Type B - bypass the ballast
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V

Temperature	
T-Case Maximum (Nom)	90 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear


Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	63 kWh

Product Data	
Order product name	63CC/LED/830/ND EX39 BB 6/1
EAN/UPC - Product	046677557171
Order code	557173
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

LED Corn Cobs

Material Nr. (12NC)	929002251814
Net Weight (Piece)	1.058 kg



Dimensional drawing



Corn lamp LED 63W EX39 830 CL


Product	D	C
63CC/LED/830/ND EX39 BB 6/1	96 mm	265 mm

Photometric data



Corn lamp LED 63W EX39 830 CL



Corn lamp LED 63W EX39 830 CL



Corn lamp LED 63W EX39 830 CL

LED Corn Cobs

Lifetime



Corn lamp LED 27W E26 830 CL

Corn lamp LED 27W E26 830 CL

