



# LED Corn Cobs

## 63CC/LED/840/ND EX39 BB 6/1

Philips Corn Cob LED replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

### Product data

General Information	
Base	EX39 [ Exclusionary Mogul Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	63-175W

Light Technical	
Color Code	841 [ CCT of 4100K (841)]
Initial lumen (Nom)	8800 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	139.00 lm/W
Color Consistency	ANSI 4000K quadrangle
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	63 W
Wattage Equivalent	175 W
Starting Time (Nom)	2.5 s
Warm Up Time to 60% Light (Nom)	2.5 s

UL Type	Type B - bypass the ballast
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V

Temperature	
T-Case Maximum (Nom)	90 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear


Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	63 kWh

Product Data	
Order product name	63CC/LED/840/ND EX39 BB 6/1
EAN/UPC - Product	046677557188
Order code	557181
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

# LED Corn Cobs

Material Nr. (12NC)	929002251914
Net Weight (Piece)	1.058 kg


## Dimensional drawing




Corn lamp LED 63W EX39 840 CL

Product	D	C
63CC/LED/840/ND EX39 BB 6/1	96 mm	265 mm


## Photometric data



Corn lamp LED 63W EX39 830 CL





Corn lamp LED 63W EX39 840 CL



Corn lamp LED 63W EX39 840 CL

# LED Corn Cobs

## Lifetime



Corn lamp LED 27W E26 830 CL

Corn lamp LED 27W E26 830 CL

