



LED Corn Cobs

120CC/LED/830/ND EX39 BB 6/1

Philips Corn Cob LED replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Product data


General Information	
Base	EX39 [Exclusionary Mogul Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	120-320W
Light Technical	
Color Code	830 [CCT of 3000K]
Initial lumen (Nom)	15500 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	129.00 lm/W
Color Consistency	ANSI 3000K quadrangle
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	120 W
Wattage Equivalent	320 W
Starting Time (Nom)	2.5 s
Warm Up Time to 60% Light (Nom)	≤2.5 s

Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	95 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	120 kWh
Product Data	
XUCDM.COPY.Product.Title	120CC/LED/830/ND EX39 BB 6/1
EAN/UPC - Product	046677553500
Order code	553503
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002252404

LED Corn Cobs

Net Weight (Piece) 1.617 kg



Dimensional drawing



Corn lamp LED 120W EX39 830 CL


Product	D	C
120CC/LED/830/ND EX39 BB 6/1	123 mm	314 mm

Photometric data



Corn lamp LED 120W EX39 830 CL



Corn lamp LED 120W EX39 830 CL



Corn lamp LED 120W EX39 830 CL

LED Corn Cobs

Lifetime



Corn lamp LED 27W E26 830 CL

Corn lamp LED 27W E26 830 CL

