



LED A15

3.3A15/VIN/820/E26/CL/GL/DIM 4/FBHT20

Philips A15 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	820 [CCT of 2000K]
Luminous Flux	200 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	60.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	3.3 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	25 W

Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	50 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Transparent amber
Bulb Material	Glass
Bulb Shape	A15 [A 15mm]

Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	No
EyeComfort	Yes


Product Data	
Order product name	3.3A15/VIN/820/E26/CL/GL/DIM 4/FBHT20
Full product name	3.3A15/VIN/820/E26/CL/GL/DIM 4/FBHT20

LED A15

Order code	929002260203
Material Nr. (12NC)	929002260203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677556556


Numerator - Packs per outer box	4
EAN/UPC - Case	50046677556551

Dimensional drawing




Product	D	C
3.3A15/VIN/820/E26/CL/GL/DIM 4/FBHT20	47 mm	84 mm


Photometric data



Light Distribution Diagram - 3.3A15/VIN/820/E26/CL/GL/DIM 4/FBHT20



Spectral Power Distribution Colour - 3.3A15/VIN/820/E26/CL/GL/DIM 4/FBHT20



Technical Parameters 13 Page Lighting ECU Page 11

General uniform lighting - 3.3A15/VIN/820/E26/CL/GL/DIM 4/FBHT20

LED A15

Lifetime



Life Expectancy Diagram - 3.3A15/VIN/820/E26/CL/GL/DIM 4/FBHT20



Lumen Maintenance Diagram - 3.3A15/VIN/820/E26/CL/GL/DIM 4/FBHT20

