



A-Shape LED

14A19/LED/850/FR/P/ND 4/2FB

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data

General Information		Wattage Equivalent	
Cap-Base	E26 [Single Contact Medium Screw]	100 W	
Nominal lifetime	11,000 hour(s)	Starting Time (Nom)	
Switching Cycle	50,000	0.5 s	
Rated Lifetime (Hours)	11,000 hour(s)	Warm-up time to 60% light	
Lighting Technology	LED	0.5 s	
EU RoHS compliant	Yes	Power Factor (Fraction)	
		0.5	
		Voltage (Nom)	
		120 V	
		Temperature	
		T-Case Maximum (Nom)	
		95 °C	
		Controls and Dimming	
		Dimmable	
		No	
		Mechanical and Housing	
		Bulb Finish	
		Frosted	
		Bulb Shape	
		A19 [A 19mm]	
		Approval and Application	
		Energy Consumption kWh/1000 h	
		14 kWh	
		EyeComfort	
		Yes	
		Product Data	
		Order product name	
		14A19/LED/850/FR/P/ND 4/2FB	
		Full product name	
		14A19/LED/850/FR/P/ND 4/2FB	
		Order code	
		929002311815	
Operating and Electrical			
Line Frequency	60 Hz		
Input Frequency	60 Hz		
Power Consumption	14 W		
Lamp Current (Nom)	255 mA		

A-Shape LED



Material Nr. (12NC)	929002311815
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677462017
Numerator - Packs per outer box	4

EAN/UPC - Case	50046677462012
----------------	----------------

Dimensional drawing


Product	D	C
14A19/LED/850/FR/P/ND 4/2FB	60 mm	117 mm

Photometric data



Spectral Power Distribution Colour - 14A19/LED/850/FR/P/ND 4/2FB


General uniform lighting - 14A19/LED/850/FR/P/ND 4/2FB



Light Distribution Diagram - 14A19/LED/850/FR/P/ND 4/2FB

A-Shape LED

Lifetime



Life Expectancy Diagram - 14A19/LED/850/FR/P/ND 4/2FB

Lumen Maintenance Diagram - 14A19/LED/850/FR/P/ND 4/2FB

