



A-Shape LED

8.5A19/PER/927-22/FR/G/WGX 4/2FB T20

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data


| General Information | | Warm-up time to 60% light | |
|---------------------------------------|-----------------------------------|---------------------------------|--------------------------------------|
| Cap-Base | E26 [Single Contact Medium Screw] | | 0.5 s |
| Nominal lifetime | 15,000 hour(s) | Power Factor (Fraction) | 0.7 |
| Switching Cycle | 20,000 | Voltage (Nom) | 120 V |
| Lighting Technology | LED | Controls and Dimming | |
| EU RoHS compliant | Yes | Dimmable | Yes |
| Light Technical | | Mechanical and Housing | |
| Color Code | 922-927 [CCT of 2200K-2700K] | Bulb Finish | Frosted |
| Luminous Flux | 800 lm | Bulb Material | Glass |
| Color Designation | Warm Glow(WG) | Bulb Shape | A19 |
| Correlated Color Temperature (Nom) | 2200 2700 K | Approval and Application | |
| Luminous Efficacy (rated) (Nom) | 94.00 lm/W | Energy Consumption kWh/1000 h | - kWh |
| Color Consistency | <4 | Energy Certifications | Energy Star |
| Color rendering index (CRI) | 90 | Product Data | |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % | Order product name | 8.5A19/PER/927-22/FR/G/WGX 4/2FB T20 |
| Operating and Electrical | | Full product name | 8.5A19/PER/927-22/FR/G/WGX 4/2FB T20 |
| Line Frequency | 60 Hz | Order code | 929002327703 |
| Input Frequency | 60 Hz | Material Nr. (12NC) | 929002327703 |
| Power Consumption | 8.5 W | Numerator - Quantity Per Pack | 1 |
| Lamp Current (Nom) | 95 mA | EAN/UPC - Product/Case | 046677557584 |
| Wattage Equivalent | 60 W | Numerator - Packs per outer box | 4 |
| Starting Time (Nom) | 0.5 s | | |

A-Shape LED

EAN/UPC - Case



50046677557589

Dimensional drawing



| Product | D | C |
|--------------------------------------|-------|--------|
| 8.5A19/PER/927-22/FR/G/WGX 4/2FB T20 | 60 mm | 108 mm |


Photometric data



Copyright: Philips Lighting B.V. Page: 17

Light Distribution Diagram - 8.5A19/PER/927-22/FR/G/WGX 4/2FB T20



General uniform lighting - 8.5A19/PER/927-22/FR/G/WGX 4/2FB T20



Spectral Power Distribution Colour - 8.5A19/PER/927-22/FR/G/WGX 4/2FB T20

A-Shape LED

Lifetime



Life Expectancy Diagram - 8.5A19/PER/927-22/FR/G/WGX 4/2FB T20

Lumen Maintenance Diagram - 8.5A19/PER/927-22/FR/G/WGX 4/2FB T20

