



# A-Shape LED

## 29A21/PER/827-22/P/E26/WG/HO 4/1FB

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

### Product data


General Information		Lamp Current (Nom)	
Cap-Base	E26 [Single Contact Medium Screw]	Lamp Current (Nom)	215 mA
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	150 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.7
EU RoHS compliant	Yes	Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	2700-2200	T-Case Maximum (Nom)	100 °C
Color Code	827-822 [tunable warm white]	Controls and Dimming	
Beam Angle (Nom)	250 degree(s)	Dimmable	Yes
Luminous Flux	2,610 lm	Mechanical and Housing	
Color Designation	Warm Glow(WG)	Bulb Finish	Frosted
Correlated Color Temperature (Nom)	2700 2200 K	Bulb Material	Plastic
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Bulb Shape	A21 [A 21mm]
Color Consistency	<6	Approval and Application	
Color rendering index (CRI)	80	EyeComfort	Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Data	
Operating and Electrical		Order product name	29A21/PER/827-22/P/E26/WG/HO 4/1FB
Line Frequency	60 Hz	Full product name	29A21/PER/827-22/P/E26/WG/HO 4/1FB
Input Frequency	60 Hz		
Power Consumption	29 W		

# A-Shape LED

Order code	929002343003
Material Nr. (12NC)	929002343003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677558222



Numerator - Packs per outer box	4
EAN/UPC - Case	50046677558227

## Dimensional drawing




Product	D	C
29A21/PER/827-22/P/E26/WG/HO 4/1FB	77 mm	138 mm

## Photometric data



Spectral Power Distribution Colour - 29A21/PER/827-22/P/E26/WG/HO 4/1FB


Light Distribution Diagram



General uniform lighting - 29A21/PER/827-22/P/E26/WG/HO 4/1FB

# A-Shape LED

## Lifetime



Life Expectancy Diagram - 29A21/PER/827-22/P/E26/WG/HO 4/1FB

Lumen Maintenance Diagram - 29A21/PER/827-22/P/E26/WG/HO 4/1FB

