


**PHILIPS**

Eco passport

## 20BR40/PER/950/E26/DIM/HO 4/1FB T20 LED BR40

Philips BR40 LED lamps are the smart alternative to standard incandescent. The traditional lamp design can provide excellent dimming performance with spectacular energy savings. They provide the beautiful light and dependable performance you expect from LED at an economical price.



### Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



#### Energy

- **Dimmable:** Yes
- **Luminous Efficacy (rated) (Nom):** 108.00 lm/W
- **Power (Rated) (Nom):** 20 W



#### Circularity

- **Nominal Lifetime (Nom):** 15000 h



#### Packaging

- **SAP Weight Paper Unit (Case):** 0.422 kg
- **SAP Weight Paper Unit (Piece):** 0.054 kg



#### Substances

- **EU REACH SVHC declaration:** Yes
- **EU RoHS compliant:** Yes



#### Weight & Materials

- **Net Weight (Piece):** 0.182 kg

Further reading at:  
<https://www.signify.com/global/sustainability/sustainable-lighting>

© 2021 Signify Holding. All rights reserved.