

PHILIPS

Eco passport

Master LEDtube HF 1200mm HO 26W 840 T5 OE MASTER LEDtube InstantFit HF T5

Philips MASTER LEDtube InstantFit T5 integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. The Philips MASTER LEDtube InstantFit T5 is the ideal solution for customers who have higher light output requirements and want to maximize value over lifetime. Full energy savings & longer lifetime result in attractive payback times and TCO benefits.



Our eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



Energy

- **Dimmable:** Yes - Check ballast compatibility
- **Energy Efficiency Label (EEL):** A++
- **Luminous Efficacy (rated) (Nom):** 150.00 lm/W
- **Power (Nom):** 26 W



Circularity

- **Nominal Lifetime (Nom):** 60000 h



Packaging

- **SAP Weight Paper Unit (Case):** 2.400 kg
- **SAP Weight Paper Unit (Piece):** 0.180 kg



Substances

- **EU REACH SVHC declaration:** Yes
- **EU RoHS compliant:** Yes



Weight & Materials

- **Net Weight (Piece):** 0.240 kg

Energy efficiency ranking / External awards



Further reading at:
<https://www.signify.com/global/sustainability/sustainable-lighting>

© 2021 Signify Holding. All rights reserved.