



Economy stick

Economy Stick 18W CDL E27 220-240 1PF/6

Entry non-covered energy saving lamp, Long life with low energy consumption.
Product consists of Philips quality at everyday low price

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	6000 h
Switching cycle	6000X
Light Technical	
Colour code	865 [CCT of 6,500 K]
Luminous flux (nom.)	1100 lm
Luminous flux (rated) (nom.)	1100 lm
Colour designation	Cool Daylight
Lumen maintenance 2,000 hours (nom.)	88 %
Chromaticity coordinate X (nom.)	313
Chromaticity coordinate Y (nom.)	337
Correlated Colour Temperature (Nom)	6500 K
Luminous efficacy (rated) (nom.)	61 lm/W
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 or 60 Hz
Power (Rated) (Nom)	18 W
Lamp current (nom.)	130 mA
Starting time (nom.)	0.3 s
Warm-up time to 60% light (min.)	5 s

Warm-up time to 60% light (max.)	40 s
Power factor (nom.)	0.6
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	No

Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (max.)	2.0 mg
Mercury (Hg) content (nom.)	1.5 mg
Energy Consumption kWh/1000 h	18 kWh

Product Data	
Full product code	871829121675900
Order product name	Economy Stick 18W CDL E27 220-240 1PF/6
EAN/UPC – product	8718291216759
Order code	21675900
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929689117001
Net weight (piece)	0.070 kg

Warnings and Safety

Economy stick

Dimensional drawing



Product	D (max)	C (max)	F (max)
Economy Stick 18W CDL E27 220-240 1PF/6	36.0 mm	143 mm	48.4 mm

ESSENGG Erp 18W CDL E27 220-240V 50/60Hz

