



Economy stick

Economy Stick 23W CDL E27 220-240 1PF/6

Entry non-covered energy saving lamp, Long life with low energy consumption.
Product consists of Philips quality at everyday low price

Product data

General Information	
Cap-Base	E27 [E27]
Nominal Lifetime (Nom)	6000 h
Switching Cycle	6000X
Light Technical	
Colour Code	865 [CCT of 6500K]
Luminous Flux (Nom)	1390 lm
Luminous Flux (Rated) (Nom)	1390 lm
Colour Designation	Cool Daylight
Lumen Maintenance 2000 h (Nom)	88 %
Chromaticity Coordinate X (Nom)	313
Chromaticity Coordinate Y (Nom)	337
Colour Temperature, horizontal (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	61 lm/W
Colour Rendering Index horiz (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 or 60 Hz
Power (Rated) (Nom)	23.0 W
Lamp Current (Nom)	160 mA
Starting Time (Nom)	0.3 s
Warm Up Time to 60% Light (Min)	5 s

Warm Up Time to 60% Light (Max)	40 s
Power Factor (Nom)	0.6
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	No


Approval and Application	
Energy Efficiency Label	A
Mercury (Hg) Content (Max)	2.0 mg
Mercury (Hg) Content (Nom)	1.5 mg
Energy Consumption kWh/1000 h	23 kWh

Product Data	
Full product code	871829121681000
Order product name	Economy Stick 23W CDL E27 220-240 1PF/6
EAN/UPC - Product	8718291216810
Order code	21681000
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929689156201
Net Weight (Piece)	0.072 kg

Warnings and Safety

Economy stick

Dimensional drawing



Product	D (max)	C (max)	F (max)
Economy Stick 23W CDL E27 220-240 1PF/6	36.0 mm	160 mm	48.4 mm

ESSENGG Erp 23W CDL E27 220-240V 50/60Hz

