



Tornado T3

Tornado T3 32W WW E27 220-240V 1PF/6

Energy-saving lamp in a decorative, spiral shape

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data


General Information			
Cap-Base	E27	Power Consumption	32.0 W
Nominal lifetime	8,000 hour(s)	Lamp Current (Nom)	140 mA
Switching Cycle	8,000	Starting Time (Nom)	0.3 s
Rated Lifetime (Hours)	8,000 hour(s)	Warm-up time to 60% light	5-40 s s
Lighting Technology	Compact Fluorescent Integrated	Power Factor (Fraction)	0.95
		Voltage (Nom)	220-240 V
Light Technical		Controls and Dimming	
Color Code	827 [CCT of 2700K]	Dimmable	No
Luminous Flux	2,255 lm		
Color Designation	Warm White (WW)	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	463	Bulb Shape	Spiral
Chromaticity Coordinate Y (Nom)	420		
Correlated Color Temperature (Nom)	2700 K	Approval and Application	
Color rendering index (CRI)	80	Mercury (Hg) Content (Max)	2.5 mg
		Mercury (Hg) Content (Nom)	2 mg
Operating and Electrical		Energy Consumption kWh/1000 h	32 kWh
Line Frequency	50 or 60 Hz		
Input Frequency	50 or 60 Hz		

Tornado T3

Product Data	
Order product name	Tornado T3 32W WW E27 220-240V 1PF/6
Full product name	Tornado T3 32W WW E27 220-240V 1PF/6
Full product code	872790087628400
Order code	87628400
Material Nr. (12NC)	929689301301

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900876284
Numerator - Packs per outer box	6
EAN/UPC - Case	8727900876291

Dimensional drawing



Product	C (max)	D (max)	F (max)
Tornado T3 32W WW E27 220-240V 1PF/6	152.5 mm	74 mm	61 mm

