



Energy Saver T2

EL/mdTQS 23W T2

The Philips EnergySaver T2 provides energy efficient lighting in a smaller, sleeker, size that fits more fixtures. The energy saving T2 is a direct replacement for most incandescents, provides soft white light and lasts 11 years* reducing the hassle of frequent replacements.


Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Nominal Lifetime (Nom)	10000 h
Switching Cycle	5000X
Light Technical	
Color Code	827 [CCT of 2700K]
Initial lumen (Nom)	1600 lm
Luminous Flux (Rated) (Nom)	1600 lm
Color Designation	Warm White (WW)
Lumen Maintenance 2000 h (Nom)	85 %
Lumen Maintenance 5000 h (Nom)	75 %
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	67 lm/W
Color Rendering Index (Min)	81
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 or 60 Hz
Power (Rated) (Nom)	23.0 W
Lamp Current (Nom)	360 mA

Power Factor (Nom)	0.55
Voltage (Nom)	110-127 V
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	2 mg
Energy Consumption kWh/1000 h	23 kWh
Product Data	
Order product name	EL/mdTQ 23W T2
EAN/UPC - Product	046677414016
Order code	414011
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929689749901
Net Weight (Piece)	0.078 kg

Energy Saver T2


Dimensional drawing



QSPIR-F 23W/827 E26 110-127V Spiral

Product

EL/mdTQ 23W T2



QSPIR-F 23W/827 E26 110-127V Spiral

Product

EL/mdTQ 23W T2

