



Energy Saver GU24

EL/mdTQS 18W GU24

Looking for an energy saver that does not look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Try the Philips EnergySavers and see how they truly provide advanced lighting designed around your needs.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	GU24 [GU24]		290 mA
Nominal lifetime	10,000 hour(s)	Power Factor (Fraction)	0.55
Switching Cycle	5,000	Voltage (Nom)	110-127 V
Rated Lifetime (Hours)	10,000 hour(s)	Controls and Dimming	
Lighting Technology	Compact Fluorescent Integrated	Dimmable	No
Light Technical		Mechanical and Housing	
Color Code	827 [CCT of 2700K]	Bulb Shape	EL/mdTQS
Luminous Flux	1,250 lm	Approval and Application	
Color Designation	Warm White (WW)	Mercury (Hg) Content (Max)	2 mg
Chromaticity Coordinate X (Nom)	459	Energy Consumption kWh/1000 h	18 kWh
Chromaticity Coordinate Y (Nom)	412	Product Data	
Correlated Color Temperature (Nom)	2700 K	Order product name	EL/mdTQS 18W GU24
Luminous Efficacy (rated) (Nom)	67 lm/W	Full product name	EL/mdTQS 18W GU24
Color rendering index (CRI)	80	Order code	454207
LLMF At End Of Nominal Lifetime (Nom)	50 %	Material Nr. (12NC)	929689791301
Operating and Electrical		Numerator - Quantity Per Pack	1
Line Frequency	50 or 60 Hz	EAN/UPC - Product/Case	046677454203
Input Frequency	50 or 60 Hz	Numerator - Packs per outer box	6
Power Consumption	18.0 W		

Energy Saver GU24

EAN/UPC - Case

50046677454208

Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/mdTQS 18W GU24	56.5 mm	104.0 mm	47 mm

