



# Energy Saver GU24

## EL/mdTQS 18W GU24

Looking for an energy saver that does not look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Try the Philips EnergySavers and see how they truly provide advanced lighting designed around your needs.

### Product data


General Information		Lamp Current (Nom)	
Cap-Base	GU24		290 mA
Nominal lifetime	10,000 hour(s)	Power Factor (Fraction)	0.55
Switching Cycle	5,000	Voltage (Nom)	110-127 V
Rated Lifetime (Hours)	10,000 hour(s)	<b>Controls and Dimming</b>	
Lighting Technology	Compact Fluorescent Integrated	Dimmable	No
<b>Light Technical</b>		<b>Mechanical and Housing</b>	
Color Code	827 [CCT of 2700K]	Bulb Shape	EL/mdTQS
Luminous Flux	1,250 lm	<b>Approval and Application</b>	
Color Designation	Warm White (WW)	Mercury (Hg) Content (Max)	2 mg
Chromaticity Coordinate X (Nom)	459	Energy Consumption kWh/1000 h	18 kWh
Chromaticity Coordinate Y (Nom)	412	<b>Product Data</b>	
Correlated Color Temperature (Nom)	2700 K	Order product name	EL/mdTQS 18W GU24
Luminous Efficacy (rated) (Nom)	67 lm/W	Full product name	EL/mdTQS 18W GU24
Color rendering index (CRI)	80	Order code	454207
LLMF At End Of Nominal Lifetime (Nom)	50 %	Material Nr. (12NC)	929689791301
<b>Operating and Electrical</b>		Numerator - Quantity Per Pack	1
Line Frequency	50 or 60 Hz	EAN/UPC - Product/Case	046677454203
Input Frequency	50 or 60 Hz	Numerator - Packs per outer box	6
Power Consumption	18.0 W		

# Energy Saver GU24

EAN/UPC - Case

50046677454208

## Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/mdTQS 18W GU24	2-1/4 inch	4-1/8 inch	1-7/8 inch

