



Energy Saver T2

EL/mdTQ 23W T2 4.1k

The Philips EnergySaver T2 provides energy efficient lighting in a smaller, sleeker, size that fits more fixtures. The energy saving T2 is a direct replacement for most incandescents, provides soft white light and lasts 11 years* reducing the hassle of frequest replacements.


Product data

General Information			
Cap-Base	E26 [Single Contact Medium Screw]		
Nominal lifetime	10,000 hour(s)		
Switching Cycle	5,000		
Rated Lifetime (Hours)	10,000 hour(s)		
Lighting Technology	Compact Fluorescent Integrated		
Light Technical			
Color Code	841 [CCT of 4100K]		
Luminous Flux	1,600 lm		
Color Designation	Cool White (CW)		
Chromaticity Coordinate X (Nom)	380		
Chromaticity Coordinate Y (Nom)	380		
Correlated Color Temperature (Nom)	4100 K		
Luminous Efficacy (rated) (Nom)	67 lm/W		
Color rendering index (CRI)	81		
LLMF At End Of Nominal Lifetime (Nom)	50 %		
Operating and Electrical			
Line Frequency	50 or 60 Hz		
Input Frequency	50 or 60 Hz		
Power Consumption	23.0 W		
Lamp Current (Nom)	360 mA		

Power Factor (Fraction)	0.55	
Voltage (Nom)	110-127 V	
Controls and Dimming		
Dimmable	No	
Mechanical and Housing		
Bulb Shape	EL/mdTQS	
Approval and Application		
Mercury (Hg) Content (Max)	2.5 mg	
Energy Consumption kWh/1000 h	23 kWh	
Product Data		
Order product name	EL/mdTQ 23W T2 4.1k	
Full product name	EL/mdTQ 23W T2 4.1k	
Order code	414060	
Material Nr. (12NC)	929689799701	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	046677414061	
Numerator - Packs per outer box	6	
EAN/UPC - Case	50046677414066	

Datasheet, 2023, November 3 data subject to change

Dimensional drawing



Product	D (max)	C (max)	F (max)
EL/mdTQ 23W T2 4.1k	2-7/16 inch	4-9/16 inch	2 inch

