



# HELIX

## HELIX 11W WW E27 220-240V 1PF/12

The Helix range is a twist-shape compact fluorescent lamp, with optimal light distribution. It is available in 11W, 15W, 20W and 23W (25W), with lumen equivalence of 60W, 75W, 100W and 125W incandescent light bulb. It is also available in two color temperatures: warm white (2700K) and cool daylight (6500K). It is available in both 220-240V and 120-127V and able to operate under a wide voltage range (Power supply fluctuation). It consumes up to 80% less energy than the incandescent light bulb and lasts for 3 years.

### Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Product data


General Information		Correlated Color Temperature (Nom)		2700 K
Cap-Base	E27 [E27]	Luminous Efficacy (rated) (Nom)	64 lm/W	
Nominal lifetime	8,000 hour(s)	Color rendering index (CRI)	82	
Switching Cycle	5,000	LLMF At End Of Nominal Lifetime (Nom)	70 %	
Rated Lifetime (Hours)	8,000 hour(s)	Operating and Electrical		
Lighting Technology	Compact Fluorescent Integrated	Line Frequency	50 or 60 Hz	
Light Technical		Input Frequency	50 or 60 Hz	
Color Code	827 [CCT of 2700K]	Power Consumption	11 W	
Luminous Flux	700 lm	Lamp Current (Nom)	80 mA	
Color Designation	Warm White (WW)	Starting Time (Nom)	0.3 s	
Chromaticity Coordinate X (Nom)	463	Power Factor (Fraction)	0.60	
Chromaticity Coordinate Y (Nom)	420			

# HELIX

<b>Voltage (Nom)</b>	220-240 V
<b>Controls and Dimming</b>	
<b>Dimmable</b>	No
<b>Mechanical and Housing</b>	
<b>Bulb Shape</b>	Spiral
<b>Approval and Application</b>	
<b>Energy Consumption kWh/1000 h</b>	11 kWh
<b>Product Data</b>	
<b>Order product name</b>	HELIX 11W WW E27 220-240V 1PF/12

<b>Full product name</b>	HELIX 11W WW E27 220-240V 1PF/12
<b>Full product code</b>	871150079741400
<b>Order code</b>	929689817399
<b>Material Nr. (12NC)</b>	929689817399
<b>Numerator - Quantity Per Pack</b>	1
<b>EAN/UPC - Product/Case</b>	8711500797414
<b>Numerator - Packs per outer box</b>	12
<b>EAN/UPC - Case</b>	8711500797490

## Dimensional drawing



Product	D (max)	C (max)	F (max)
HELIX 11W WW E27 220-240V 1PF/12	47.0 mm	116.0 mm	44.4 mm

