

# PHILIPS

Bulb

LED

9-3-1W-60W

E26

Daylight

046677464912



## State-of-the-art LED for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High quality light

- Learn about light
- No visible flicker

### Create the right light for your home

- A simple LED for everyday use

### Light beyond illumination

- Three light settings

# Highlights

## Learn about light



Color temperature: light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more tranquil light, while those with a higher Kelvin value produce a cool, more energizing light. CRI: the color

rendering index (CRI) is used to describe the effect of a light source on color appearance. Natural sunlight has a CRI of 100. The CRI of Philips LED light bulbs is always higher than 80, which ensures colors are shown as true and natural.

### No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

### A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

### Three light settings (SSDL)

All-in one replacement bulb that changes between three different brightness levels of Daylight, all with your existing switch.

# Specifications

## Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 11.1 cm
- Weight: 0.055 kg
- Width: 6.1 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 100,000

## Light characteristics

- Beam angle: 200 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 800-320-80 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 850 | CCT of 5000K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 130 mA
- Efficacy: 88 lm/W

## Packaging information

- EAN: 046677464912
- EOC: 464917
- Product title: 9A19/AMB/850/ND SSDL 120V 4/1BC

#### Power consumption

- Power factor: 0.6
- Voltage: 120 V
- Wattage: 9, 3, 1 W
- Wattage equivalent: 60 W

#### Product dimensions & weight

- Length: 11.1 cm

#### Rated values

- Rated beam angle: 200 degree(s)
- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 800-320-80 lumen
- Rated power: 9-3-1 W

#### Technical specifications

- Frequency: 50-60 Hz

#### Packaging dimensions and weight

- EAN/UPC - product: 046677464912
- Net weight: 0.062 kg
- Gross weight: 0.081 kg
- Height: 18.400 cm
- Length: 6.600 cm
- Width: 14.000 cm
- Material number (12NC): 929001261465



Issue date: 2021-06-29  
Version: 0.218

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)