

# PHILIPS

Capsule

LED

1.2W-7W

Wedgebase

Bright White

046677475543



## Designed to be seen

With its beautifully shaped design and familiar dimensions, this LED spot is the perfect sustainable replacement for a traditional halogen spot.

### High quality light

- Bright white light

### Choose for a sustainable solution

- Saves up to 80% Energy

# Highlights

## Bright white light



This bulb has a color temperature of 3000K providing you with a bright,

warm light, perfect for creating an inviting ambiance to host friends or wind down with a book.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional capsule
- Socket: Wedgebase
- Technology: LED

## Bulb dimensions

- Height: 3.4 cm
- Weight: 0.004 kg
- Width: 1.3 cm

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Light Color Category: Bright White
- Nominal luminous flux: 120 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: instant full light
- Color Code: 830 | CCT of 3000K

## Miscellaneous

- EyeComfort: No

## Other characteristics

- Lamp current: 138 mA
- Efficacy: 100 lm/W

## Packaging information

- EAN: 046677475543
- EOC: 533455
- Product title: 1.2T5/SPC/830/ND/12V/BC/2PK 6/2

## Power consumption

- Energy Star Certified: No
- Power factor: 0.57
- Voltage: 12V AC electronic V
- Wattage: 1.2 W
- Wattage equivalent: 7 W

## Product dimensions & weight

- Length: 3.4 cm

## Rated values

- Rated lifetime: 15,000 hour(s)
- Rated luminous flux: 120 lumen
- Rated power: 1.2 W

## Technical specifications

- Frequency: - Hz

**Packaging dimensions and weight**

- EAN/UPC - product: 046677475543
- Net weight: 0.016 kg
- Gross weight: 0.031 kg
- Height: 13.500 cm
- Length: 1.500 cm
- Width: 10.000 cm
- Material number (12NC): 929002389596



Issue date: 2023-11-08  
Version: 0.18

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)