

PHILIPS

Spot

LED

10W (18W)

E26

Daylight

Non-dimmable



046677532963



Enhanced plant growth in a beautiful white light

Philips LED Plant Grow lights not only optimize plant growth but also provide a beautiful, natural look for your plants. Full Spectrum White - the perfect color spectrum for growth and natural color.

Application areas

- The perfect color spectrum for growth and a natural look
- UL Wet Rated

Long life

- Long life bulbs - Lasts up to 25 years
- CRI90 shows colors more vibrantly

Highlights

Grow Light Spectrum

Focus on the blue wavelength helps to promote optimum plant and vegetative growth. Full spectrum with white color delivers healthy growth and a beautiful natural appearance.

UL Wet Rated

This LED bulb can be used in indoor and outdoor applications. It is wet rated and outdoor safe.

25,000-hour rated average life



With a lifetime of up to 25,000 hours, you can reduce the hassle of

frequently replacing your light bulbs and enjoy a perfect lighting solution for over 25 years.

CRI90

This LED bulb has a color rendering index (CRI) of 90. CRI measures how well a light source displays colors in comparison to natural sunlight, and has a range from 0 to 100, with 100 being the closest to sunlight. This CRI90 bulb will help the colors in your home appear more natural and vibrant.

Specifications

Characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E26
- Technology: LED

Bulb dimensions

- Height: 13.2 cm
- Weight: 0.38 kg
- Width: 12.2 cm

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Nominal lifetime: 2,500 hour(s)
- Number of switch cycles: 5,000

Light characteristics

- Beam angle: 50 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 5000 K
- Light Color Category: Daylight
- Nominal luminous flux: 1200 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Other characteristics

- Lamp current: 150 mA
- Efficacy: 75 lm/W

Power consumption

- Power factor: 0.9
- Voltage: 110–240 V
- Wattage: 24 W

Product dimensions & weight

- Length: 120 cm

Rated values

- Rated beam angle: 50 degree(s)
- Rated lifetime: 25,000 hour(s)
- Rated luminous flux: 1200 lumen
- Rated peak intensity: 600 cd
- Rated power: 16 W

Technical specifications

- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC – product: 046677532963
- Net weight: 0.370 kg
- Gross weight: 0.530 kg
- Height: 16.700 cm
- Length: 13.200 cm
- Width: 13.200 cm
- Material number (12NC): 929001892703



Issue date: 2023-11-08
Version: 0.403

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com