

PHILIPS

Bulb

LED

6.5W-40W

E26

Soft White

046677565428



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Long life bulb - Lasts up to 10 years

Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

10,950-hour rated average life

With a lifetime of up to 10,950 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 10 years.

Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Type of glass: Frosted
- Bulb Finish: Frosted
- Bulb Material: Plastic

Bulb dimensions

- Height: 10.4 cm
- Width: 6 cm

Design and finishing

- Material: Plastic

Durability

- Nominal lifetime: 11,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Nominal luminous flux: 450 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 927 | CCT of 2700K
- Correlated Color Temperature (Nom): 2700 K
- Luminous Efficacy (rated) (Nom): 69.00 lm/W
- Luminous Flux: 450 lm

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 69 lm/W
- EU RoHS compliant: Yes

Packaging information

- EAN: 046677565428
- EOC: 565424
- Product title: 6.5A19/LED/927/FR/P/E26/ND 4/2CT

Power

- Power Factor (Fraction): 0.5

Power consumption

- Energy Star Certified: No
- Power factor: 0.5
- Voltage: 120 V
- Wattage: 6.5 W
- Wattage equivalent: 40 W
- Power Consumption: 6.5 W

Product dimensions and weight

- Length: 10.4 cm

Rated values

- Rated lifetime: 11,000 hour(s)

Technical specifications

- Frequency: 60 Hz
- Dimmable: No
- Line Frequency: 60 Hz
- Cap-Base: E26 | Single Contact Medium Screw
- UL Wet/ damp/ dry location: Damp location

Packaging dimensions and weight

- EAN/UPC – product: 046677565428
- Net weight: 0.06 kg
- Gross weight: 0.09 kg
- Height: 10.7 cm
- Length: 6.2 cm
- Width: 10 cm
- Material number (12NC): 929003004503



Issue date: 2024-02-06
Version: 0.34

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com