

# PHILIPS

Bulb

LED

14W-100W

E26

Soft White

046677565503



## A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High quality light

- Long life bulb - Lasts up to 10 years

### Choose a simple replacement for your old bulbs

- Similar shape and size as standard incandescent bulb

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## 10,950-hour rated average life

With a lifetime of up to 10,950 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 10 years.

## Replaces standard incandescent

With its beautiful design and familiar shape, this energy-saving LED bulb is the perfect sustainable replacement for traditional incandescent bulbs.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get

glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Technology: LED
- Type of glass: Frosted

## Bulb dimensions

- Height: 11.7 cm
- Weight: 0.045 kg
- Width: 6 cm

## Durability

- Average life (at 2.7 hrs/day): 11 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 11,000 hour(s)
- Number of switch cycles: 50,000

## Light characteristics

- Beam angle: 150 degree(s)
- Color consistency: 6SDCM
- Color rendering index (CRI): 90
- Color temperature: 2700 K
- Light Color Category: Soft White
- Nominal luminous flux: 1500 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 927 | CCT of 2700K

## Miscellaneous

- EyeComfort: Yes

## Other characteristics

- Lamp current: 223 mA
- Efficacy: 107 lm/W

## Packaging information

- EAN: 046677565503
- EOC: 565507
- Product title: 14A19/LED/927/FR/P/E26/ND 4/2CT

## Power consumption

- Energy Star Certified: No
- Power factor: 0.5
- Voltage: 120 V
- Wattage: 14 W
- Wattage equivalent: 100 W

## Product dimensions & weight

- Length: 11.7 cm

## Rated values

- Rated beam angle: 150 degree(s)
- Rated lifetime: 11,000 hour(s)
- Rated luminous flux: 1500 lumen
- Rated power: 14 W

## Technical specifications

- Frequency: 60 Hz

**Packaging dimensions and weight**

- EAN/UPC - product: 046677565503
- Net weight: 0.100 kg
- Gross weight: 0.128 kg
- Height: 11.500 cm
- Length: 6.200 cm
- Width: 10.000 cm
- Material number (12NC): 929003005403



Issue date: 2022-07-21  
Version: 0.32

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)