

PHILIPS

Candle & Lustre
(Dimmable)

LED


8W-75W

E26

Warm Glow

Dimming

046677566364



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Designed for the comfort of your eyes

Designed to be seen, looks good on and off

- Classic glass LED

Highlights

Gentle LEDs, easy on the eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get the glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Glass Clear Design

The look you love, the performance you expect. Classic clear glass designs that replicate the beautiful sparkling light of traditional bulbs, for a perfect fit throughout your home.

Specifications

Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor/Outdoor
- Lamp shape: Non directional bulb
- Socket: E26
- Type of glass: Clear
- Bulb Finish: Clear

Bulb dimensions

- Height: 13.7 cm
- Width: 6.4 cm

Durability

- Nominal lifetime: 15,000 hour(s)
- Number of switch cycles: 20,000

Light characteristics

- Beam angle: 300 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 2200-2700 K
- Nominal luminous flux: 800 lm
- Warm-up time to 60% light: instant full light
- Color Code: 922-927 | CCT of 2200K-2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 100 lm/W

Packaging information

- EAN: 046677566364
- EOC: 566364
- Product title: 8ST19/VIN/927-922/CL/G/E26/WGD 4/4PF T20

Power consumption

- Energy Star Certified: No
- Power factor: 0.7
- Voltage: 120 V
- Wattage: 8 W
- Wattage equivalent: 75 W

Product dimensions and weight

- Length: 13.7 cm

Technical specifications

- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677566364
- Net weight: 0.18 kg
- Gross weight: 0.3 kg
- Height: 17.9 cm
- Length: 7 cm
- Width: 27.5 cm
- Material number (12NC): 929002296013



Issue date: 2024-02-02
Version: 0.52

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com