

PHILIPS

Reflector

LED

13.5 W

E26

Blue

046677568269



State-of-the-art LED for the home

Party light for creating nice atmosphere at home

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor/Outdoor
- Lamp shape: Directional reflector
- Socket: E26
- Technology: LED

Bulb dimensions

- Height: 13.2 cm
- Weight: 0.44 kg
- Width: 12.2 cm

Durability

- Average life (at 2.7 hrs/day): 11 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 10,950 hour(s)
- Number of switch cycles: 10,000

Light characteristics

- Light Color Category: Blue
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 165 mA

Packaging information

- EAN: 046677568269
- EOC: 568261
- Product title: 13.5PAR38/PER/
BLUE/G/E26/ND/ULW 3/1PF

Power consumption

- Energy Star Certified: No
- Power factor: 0.5
- Voltage: 120 V
- Wattage: 13.5 W

Product dimensions & weight

- Length: 13.2 cm

Rated values

- Rated lifetime: 10,950 hour(s)
- Rated power: 13.5 W

Technical specifications

- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677568269
- Net weight: 0.350 kg
- Gross weight: 0.442 kg
- Height: 20.900 cm
- Length: 13.000 cm
- Width: 13.000 cm
- Material number (12NC):
929001306533



Issue date: 2022-07-21
Version: 0.46

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com